













# DUST CONTROL SYSTEMS

The best tools, vacuums, and dust removal accessories to help clear the air, add productivity on the jobsite and help meet OSHA 1926.1153 Table 1 compliance.

APPLICATION	TOOLS AND VACUUMS																DUST CONTROL ACCESSORY		
SDS+ DRILLING / CHISELING	Rotary hammers										Universal vacuum cleaners						Hollow drill bit	Dust removal system	
	TE 2-A	TE 3-C	TE 7-C	TE 30-C	TE 30-A	TE 4-A	TE 6-A22	TE 6-A36	VC 75-1-A22 <sup>1</sup>	VC 125-6	VC 125-9	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X	TE-CD	DRS-D	DRS-C
	2149902	3553166	3476284	3578572	3567671	3482498	3577891	3551238	2187661	2167148	2167149	3721395	2220086	3720112	3721394	3563662		2191207	2213351
SDS-MAX DRILLING / CHISELING	Combihammer							Universal vacuum cleaners						Hollow drill bit	Dust removal system				
	TE 50	TE 60-AVR	TE 60-ATC	TE 60-A36	TE 70	TE 70-ATC	TE 80-ATC	VC 75-1-A22 <sup>1</sup>	VC 125-6	VC 125-9	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X	TE-YD	TE DRS-Y	DRS-D	
	3553052	3564151	3564152	2191223	3514170	3514171	2083438	2187661	2167148	2167149	3721395	2220086	3720112	3721394	3563662		2055718	2191207	
CONCRETE BREAKING	Breaker								Universal vacuum cleaners						Dust removal system				
	TE 300-A36	TE 500-A36	TE 500-AVR	TE 700-AVR	TE 800-AVR	TE 1000-AVR	TE 2000-AVR	TE 3000-AVR	VC 75-1-A22 <sup>1</sup>	VC 125-6	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X	DRS-B			
	3609658	2237133	3512856	3484793	3531084	3523418	3578530	3492616	2187661	2167148	2167149	3721395	2220086	3720112	3721394	3563662	365944		
CONCRETE CUTTING AND GRINDING	Angle grinder					Universal vacuum cleaners						Tuck pointing/cutting	Grinding	Slitting					
	AG 450-S	AG 450-D	AG 500-12D	AG 500-11S	AG 700-14D	VC 125-6	VC 125-9	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X	4.5"	5"	4.5"	5"	5"		
	2075613	2075614	3564653	3564654	3578887	2167148	2167149	3721395	2220086	3720112	3721394	3563662	2101312	284978	2102983	2126539	267720		
	Diamond grinder		Diamond cutter			Universal vacuum cleaners					DCH depth gauge/dust shroud								
DGH 130	DG 150	DCH 230 <sup>4</sup>	DCH 300-X Wet/Dry <sup>4</sup>	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X	DCH 230		DCH 300-X								
2194877	369388	3444488	2149601	3721395	2220086	3720112	3721394	3563662	212187		212131								
CONCRETE CORING <sup>3</sup>	Diamond coring tool		Universal vacuum cleaners						Adapter	SPX-Masonry									
	DD 110-W	DD 150-U	VC 125-6	VC 125-9	VC 150-6 X	VC 150-10 X	VC 150-6 XE	VC 150-10 XE	VC 300-17 X										
	2087491	3483121	2167148	2167149	3721395	2220086	3720112	3721394	3563662	315826									
	Diamond coring tool		Water Management System				DWP 10 tank												
DD 30-W	DD 120	DD 150-U	DD 160-U	DD 250	DD 350-CA	DD 500-CA	WMS 100												
2043846	274935	3483076	3496301	3550349	3536957	3536965	3575546	365595											
CONCRETE SAWING	Hand-held gas saw						DSH-P	DWP 10 tank	Floor saw cart										
	DSH 600-X	DSH 700-X	DSH 900-X																
	2136539	2121540	2121542	2124505	365595	431364													

1 Hilti's manufacturer guidelines state that the VC-75-1-A22 can be used for cleaning and drilling extraction for TE-C drills (SDS-Plus) and TE-Y (SDS-Max). When used with the DRS-D with a SDS-Max tool, the VC-75 can be used for dust collection when drilling diameters up to 32 mm (1.25") on wall and floor applications.  
 2 The published item numbers here will provide OSHA 1926.1153 Table 1 compliant solutions. Previous generations will still need to utilize the objective data test report. Call Hilti for additional questions.  
 3 Hilti interprets a core drill as also being a OSHA 1926.1153 Table 1 (v) "dry", and therefore DD 110 and DD 150 and/or other hand held core drills are compliant when used with a shroud and dust collection system.  
 4 Hilti interprets these tools as large handheld angle grinders, which would therefore place them in OSHA 1926.1153 Table 1 section (ii). These tools are OSHA 1926.1153 Table 1 compliant ONLY when used with the VC 300-17 X. However, you can use Hilti's objective data test report when using the VC 150 vacuums  
 5 OSHA 1926.1153 Table 1 engineering control method as specified in 29 CFR 1926.1153. Core drills under OSHA 1926.1153 Table 1 (v) "rig mounted core drills" are compliant when stand-mounted and used with a water delivery system.

Description	Item Number												
		VC 75 A-22	VC 125-6	VC 125-9	VC 150-6 X Gen 1	VC 150-10 X Gen 1	VC 150-6 XE Gen 1	VC 150-10 XE Gen 1	VC 150-6X Gen 2	VC 150-10X Gen 2	VC 150-6 XE Gen 2	VC 150-10XE Gen 2	VC 300-17 X
Filter VC 300 standard dry	2177885												■
Filter VC 300 HEPA (wet/dry)	2177708												■
Filter VC 125 / 150 standard (dry)	2121386		■	■	■	■	■	■					
Filter VC 125 / 150 universal (wet/dry)	2121387		■	■	■	■	■	■					
Filter VC 125 / 150 HEPA (wet/dry)	203879		■	■	■	■	■	■					
Filter VC 75 (dry)	2192229	■											
Filter VC 75 HEPA	2192228	■											
Filter Dry VC 20/40/150 Standard	2278640							■	■	■	■		
Filter Universal VC 20/40/150 Premium	2261257							■	■	■	■		
Filter HEPA VC 20/40/150 Ultimate	2261452							■	■	■	■		
Plastic bags VC 300 (10 pk)	2177881												■
Plastic bags VC 150-6 (10 pk)	203854				■		■						
Plastic bags VC 150-10 (10 pk)	203852					■			■				
Plastic bags VC 125-6 (10 pk)	2177709		■										
Plastic bags VC 125-9 (10 pk)	2177880			■									
Fleece bags VC 300 (5 pk)	2177884												■
Fleece bags VC 150-6 (5 pk)	2121560				■		■						
Fleece bags VC 150-10 (5 pk)	2121562					■			■				
Fleece bags VC125-6 (5 pk)	2177882		■										
Fleece bags VC 125-9 (5 pk)	2177883			■									
Fleece bags VC 75 (5 pk)	2192260	■											
Paper bags VC 150-6 [5 pk]	203858				■		■						
Paper bags VC 150-10 (5 pk)	203856					■			■				
Dust bag fleece VC 20/150-6 Premium	2261258							■	■	■	■		
Dust bag fleece VC 40/150-10 Premium	2262130							■	■	■	■		
Dust bag plastic VC 20M Ultimate	2261451							■	■	■	■		
Dust bag plastic VC 40M Ultimate	2262095							■	■	■	■		
Y Splitter	2194689		■	■	■	■	■	■	■	■	■	■	■
VC 300-17X Water Diffuser	2224567							■	■	■	■	■	■
Anti-static Vacuum Hose 16'	203867		■	■	■	■	■	■	■	■	■	■	■
Hose VC 75	2213354	■						■	■	■	■	■	■
VC 75 floor brush-nozzle attachment	2206016	■						■	■	■	■	■	■
VC 75 Backpack	2224566	■						■	■	■	■	■	■
Accessory Kit VC 75	2210799	■						■	■	■	■	■	■
Universal Conical Adapter	2214620		■	■	■	■	■	■	■	■	■	■	■
Vac Accessory Set (Premium)	2044213		■	■	■	■	■	■	■	■	■	■	■
Vac Accessory Set (Econ)	2182583		■	■	■	■	■	■	■	■	■	■	■
Push Bar for VC 150-6 / VC 20	2044214				■	■	■	■	■	■	■	■	■
Vacuum Clamping Set VC 150	2049552				■	■	■	■	■	■	■	■	■
Adapter Plate for VC 150	2044211				■	■	■	■	■	■	■	■	■
Tool Box (Adapter Plate required)	2044212				■	■	■	■	■	■	■	■	■
DG 150 Hose Coupling	281862		■	■	■	■	■	■	■	■	■	■	■
Accessory storage bag VC	2271512							■	■	■	■	■	■
Shoulder strap VC 20	2276922							■	■	■	■	■	■