



NUN 54-22

AL-type dies



NUN 54-22 IE-A22 with jaw NCR J SU and NCR SU AL-type dies selection

Dies for aluminum connectors				Number of crimps per connector ¹					
Type	Item no.	Wire size	Color code	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B
NCR SU AL 8	2183656	8 AWG	Blue					N/A	
NCR SU AL 6	2183657	6 AWG	Gray						
NCR SU AL 4	2183658	4 AWG	Green	2	2	2	2	2	2
NCR SU AL 2	2183659	2 AWG	Pink						
NCR SU AL	2183660	1 AWG	Gold						
NCR SU AL 1/0	2183661	1/0 AWG	Tan						
NCR SU AL 2/0	2183662	2/0 AWG	Olive	3	3	3	3	3	3
NCR SU AL 3/0	2183663	3/0 AWG	Ruby						
NCR SU AL 4/0	2183664	4/0 AWG	White						
NCR SU AL 250	2183665	250 MCM	Red						
NCR SU AL 300	2183666	300 MCM	Blue	4	4	4	4	4	4
NCR SU AL 350	2183667	350 MCM	Brown						

¹ Use the number of crimps listed in this column instead of the number provided with the connector

When used with NCR SU AL-type dies, the tool (NUN 54-22 IE-A22 with the crimping jaw NCR J SU) is cULus classified for use with the following connector brands.

Connector type	Barrel type	Anderson	Blackburn®	Burndy	ILSCO	Panduit ²	T&B
Dual-rated Aluminum Splice	-	VACS	ASP	YS-A	AS	SA	60501-60565
Dual-rated Aluminum Lug	-	VACL	ATL	YA-A YA-ATN	ACL/ACN 2ACL/2ACN	LAA/LAB	60101-60166 60230-60267

² 6 AWG to 360 MCM

