

Tub Box Kit CP 681

Product description

- Standard 2" device accepts a pass-through 1-1/2" pipe (with a sealing bushing) or a standard 2" P-trap (direct connection to the coupling)
- Standard 3" accepts a pass-through 2" and can be adapted for smaller pass-through pipes
- One system for virtually all pipe materials, easy to choose and inspect
- Creates a 2-1/2" deep recess in the slab

Applications for use

- Can be used with bath tubs and jacuzzi drains
- Accessories available for extended heights and elongated box outs (for jacuzzi drains)

Installation instructions

- See Hilti Literature or third-party listings for complete application and installation details



Tub Box, Classic 2 Inch (Standard)



Tub Box, 3 Inch (Standard)

Technical data	
Color	Red
Height	8 in
Dimensions (LxWxH)	14.4 x 10.7 x 8
Mold and mildew performance	Class 0 (ASTM G21-96)
Temperature resistance range	-4 - 212 °F
Expansion temperature (Approx.)	410 °F
Expansion ratio (unrestricted, up to)	1:19
Storage and transportation temperature range	23 - 122 °F
Application temperature range	23 - 122 °F
Intumescent	Yes
Tested in accordance with	UL 1479 ASTM E 814 ASTM G 21



Order Designation	Sales pack quantity	Item number
Tub Box, Classic 2 Inch (Standard)	1 pc	295455
Tub Box, 3 Inch (Standard)	1 pc	295456