

5.0 Installation System Hangers

Strut clamp – rigid (SS 316)

Product Features

- For use with rigid stainless steel pipes

Material Specifications

Material	316 Stainless Steel
Conforms with	<ul style="list-style-type: none"> • Federal specifications WW-H-171E (Type 59) • Manufacturers Standardization Society MSS-SP-58 (Type 59)



Ordering Information / Technical Information

Description	Allowable Load 1 (lb) ¹	Allowable Load 2 (lb) ¹	Allowable Load 3 (lb) ¹	Box Qty	Item No.
Strut Clamp Rigid 1/2" SS316	400	75	50	50	424215
Strut Clamp Rigid 3/4" SS316	400	75	50	50	424216
Strut Clamp Rigid 1" SS316	600	75	50	50	424217
Strut Clamp Rigid 1-1/4" SS316	600	75	50	25	424218
Strut Clamp Rigid 1-1/2" SS316	600	75	50	25	424219
Strut Clamp Rigid 2" SS316	600	75	50	25	424220
Strut Clamp Rigid 2-1/2" SS316	800	75	50	10	424221
Strut Clamp Rigid 3" SS316	800	75	50	10	424222
Strut Clamp Rigid 4" SS316	1000	75	50	10	424223

¹ Based on a safety factor of 3. Allowable loads are based on loading in one direction only.

