



CORDLESS STUD FUSION / Ordering Guide



Tool		
Item Number	Description	Details
3859942	CSF Tool Kit, FX 3-A, Charger & HT Kit	Surfacing tool (SF 6h-22) not included

Individual CSF Tool Items (#3859942)		
2270478	FX 3-A	Included in Combo #3859942
2270521	Battery charger C 53 110V-120V 50/60 Hz	Included in Combo #3859942
2293909	Starter kit FX 3-KIT	Included in Combo #3859942 Hand tool with accessories

Surfacing Tool (not included in Combo #3859942)		
2254917	SF 6H-22 Nuron	
2251352	Battery Pack B 22-85 Li-ion Nuron	
2253927	Nuron Battery Charger C 4-22 115V	

Gas Cans and Surfacing Bits		
2241926	Gas can GC FX 3	Approx. 100 fastenings per can
2270512	Surfacing tool post-pain FX 3-ST d20	Approx. 200 surfacings per bit
2270514	Surfacing tool pre-paint FX 3-ST d14	Approx. 350 surfacings per bit



CORDLESS STUD FUSION / Ordering Guide

Studs			
Item Number	Description	Box Qty	Details
2293829	Threaded stud F-BT-MR M6x25 SN (6)	200	Post-paint: Includes sealing washer + safety flange nut
2293866	Threaded stud F-BT-MR M6x25 (6)	1500	Pre-paint: washer + nut not included
2293880	Threaded stud F-BT-MR 3/8x1 SN (3/8)	200	Post-paint: Includes sealing washer + safety flange nut
2293881	Threaded stud F-BT-MR 3/8x1-1/2 SN (3/8)	100	Post-paint: Includes sealing washer + safety flange nut
2293882	Threaded stud F-BT-MR 3/8x2 SN (3/8)	100	Post-paint: Includes sealing washer + safety flange nut
2293883	Threaded stud F-BT-MR 3/8x4 SN (3/8)	100	Post-paint: Includes sealing washer + safety flange nut
2293887	Threaded stud F-BT-MR 3/8x1 SN (5/32)	200	Post-paint: Includes sealing washer + safety flange nut
2293890	Threaded stud F-BT-MR 3/8x1 (3/8)	1000	Pre-paint: washer + nut not included
2293891	Threaded stud F-BT-MR 3/8x1-1/2 (3/8)	800	Pre-paint: washer + nut not included
2293892	Threaded stud F-BT-MR 3/8x2 (3/8)	700	Pre-paint: washer + nut not included
2293893	Threaded stud F-BT-MR 3/8x4 (3/8)	400	Pre-paint: washer + nut not included
2293895	Threaded stud F-BT-MR 1/2x1-1/2 (3/8)	500	Pre-paint: washer + nut not included
2293896	Threaded stud F-BT-MR 1/2x2 (3/8)	400	Pre-paint: washer + nut not included
2293894	Threaded stud F-BT-MR M6x25 SN (4)	200	Post-paint: Includes sealing washer + safety flange nut



CORDLESS STUD FUSION / Ordering Guide

Standard Hex Nuts + Flat Washers (not Flange Nuts or Sealing Washers)

Item Number	Description	Box Qty	Details
411775	Hexagon Nut 3/8" SS316	100	
411780	Washer 3/8" x 13/16" SS316	200	Washer Outer Diameter = 13/16"
411785	Washer 3/8" x 1-1/2" SS316	100	Washer Outer Diameter = 1-1/2"
411776	Hexagon Nut 1/2" SS316	100	
411781	Washer 1/2" x 1-1/16" SS316	100	Washer Outer Diameter = 1-1/16"
411787	Washer 1/2" x 2" SS316	100	Washer Outer Diameter = 2"



CORDLESS STUD FUSION / Ordering Guide

Coated Steel Consumable Combos using Sealing Washers

Combo Information		What is included in the combo			
Combo Item Number	Combo Description		Item #	Stud Description	Qty in Combo
3895377	F-BT-MR M6x25 SN (6) with sealing washer for coated base material	Studs	2293829	F-BT-MR M6x25 SN (6)	200
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	2
3895378	F-BT-MR 3/8x1 SN (3/8) with sealing washer for coated base material	Studs	2293880	F-BT-MR 3/8x1 SN (3/8)	200
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	2
3895379	F-BT-MR 3/8x1-1/2 SN (3/8) with sealing washer for coated base material	Studs	2293881	F-BT-MR 3/8x1-1/2 SN (3/8)	100
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	1
3895380	F-BT-MR 3/8x2 SN (3/8) with sealing washer for coated base material	Studs	2293882	F-BT-MR 3/8x2 SN (3/8)	100
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	1
3895381	F-BT-MR 3/8x4 SN (3/8) with sealing washer for coated base material	Studs	2293883	F-BT-MR 3/8x4 SN (3/8)	100
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	1
3895382	F-BT-MR 3/8x1 SN (5/32) with sealing washer for coated base material	Studs	2293887	F-BT-MR 3/8x1 SN (5/32)	200
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	2
3895883	F-BT-MR M6x25 SN (4) with sealing washer for coated base material	Studs	2346394	F-BT-MR M6x25 SN (4)	200
		Bits	2270512	FX 3-ST d20	1
		Gas Cans	2241926	Gas can GC FX 3	2



CORDLESS STUD FUSION / Ordering Guide

Coated Steel Consumable Combos with Touch-Up (no Sealing Washer)

Combo Information		What is included in the combo			
Combo Item Number	Combo Description		Item #	Stud Description	Qty in Combo
3895884	F-BT-MR M6x25 (6) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293866	F-BT-MR M6x25 (6)	1500
		Bits	2270512	FX 3-ST d20	8
		Gas Cans	2241926	Gas can GC FX 3	15
3895885	F-BT-MR 3/8x1 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293890	F-BT-MR 3/8x1 (3/8)	1000
		Bits	2270512	FX 3-ST d20	5
		Gas Cans	2241926	Gas can GC FX 3	10
3895886	F-BT-MR 3/8x1-1/2 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293891	F-BT-MR 3/8x1-1/2 (3/8)	800
		Bits	2270512	FX 3-ST d20	4
		Gas Cans	2241926	Gas can GC FX 3	8
3895887	F-BT-MR 3/8x2 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293892	F-BT-MR 3/8x2 (3/8)	700
		Bits	2270512	FX 3-ST d20	4
		Gas Cans	2241926	Gas can GC FX 3	7
3895888	F-BT-MR 3/8x4 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293893	F-BT-MR 3/8x4 (3/8)	400
		Bits	2270512	FX 3-ST d20	2
		Gas Cans	2241926	Gas can GC FX 3	4
3895889	F-BT-MR 1/2x1-1/2 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293895	F-BT-MR 1/2x1-1/2 (3/8)	500
		Bits	2270512	FX 3-ST d20	3
		Gas Cans	2241926	Gas can GC FX 3	5
3895890	F-BT-MR 1/2x2 (3/8) without sealing washer for coated base material. Installer responsible for touch-up.	Studs	2293896	F-BT-MR 1/2x2 (3/8)	400
		Bits	2270512	FX 3-ST d20	2
		Gas Cans	2241926	Gas can GC FX 3	4



CORDLESS STUD FUSION / Ordering Guide

Uncoated Steel Consumable Combos

Combo Information		What is included in the combo			
Combo Item Number	Combo Description		Item #	Stud Description	Qty in Combo
3895891	F-BT-MR M6x25 (6) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293866	F-BT-MR M6x25 (6)	1500
		Bits	2270514	FX 3-ST d14	5
		Gas Cans	2241926	Gas can GC FX 3	15
3895892	F-BT-MR 3/8x1 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293890	F-BT-MR 3/8x1 (3/8)	1000
		Bits	2270514	FX 3-ST d14	4
		Gas Cans	2241926	Gas can GC FX 3	10
3895893	F-BT-MR 3/8x1-1/2 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293891	F-BT-MR 3/8x1-1/2 (3/8)	800
		Bits	2270514	FX 3-ST d14	3
		Gas Cans	2241926	Gas can GC FX 3	8
3895894	F-BT-MR 3/8x2 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293892	F-BT-MR 3/8x2 (3/8)	700
		Bits	2270514	FX 3-ST d14	3
		Gas Cans	2241926	Gas can GC FX 3	7
3895895	F-BT-MR 3/8x4 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293893	F-BT-MR 3/8x4 (3/8)	400
		Bits	2270514	FX 3-ST d14	2
		Gas Cans	2241926	Gas can GC FX 3	4
3895896	F-BT-MR 1/2x1-1/2 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293895	F-BT-MR 1/2x1-1/2 (3/8)	500
		Bits	2270514	FX 3-ST d14	2
		Gas Cans	2241926	Gas can GC FX 3	5
3895897	F-BT-MR 1/2x2 (3/8) for uncoated base material. Installer responsible for corrosion protection.	Studs	2293896	F-BT-MR 1/2x2 (3/8)	400
		Bits	2270514	FX 3-ST d14	2
		Gas Cans	2241926	Gas can GC FX 3	4