



A = 1" (25mm)
 B ≥ 1-3/16" (30mm)
 C ≤ 3/16" (4.8mm)

X-MGR-W60 SELECTION GUIDE FOR GRATING		
GRATING HEIGHT In. (mm)	FASTENER DESCRIPTION	ITEM NO.
1 (25) - 1-1/2 (38)	X-MGR-W60	384234