



*Some limitations apply. Contact Hilti for details.

- ### Applications
- Transferring reference heights
 - Aligning pipes
 - Leveling junction boxes, cable trays, radiators and pipe installations
 - Leveling and aligning doors and windows
 - Setting out drywall tracks for partitioning
 - Transferring fastening points from floors to ceilings

- ### Outperform
- Leveling, aligning, plumbing and squaring — all in one tool
 - Pulse Power™ technology for reliable, accurate measurements at the touch of a button
 - Innovative universal adapter and compact tripod for placing or mounting the tool wherever needed

- ### Outlast
- Impact Protection System (IPS) with a sturdy inner pendulum housing
 - Rubberized drop points designed to withstand tough jobsite conditions
 - Supported by Hilti Lifetime Service which includes the outstanding 2 year No-Cost Coverage

The professional's full solution.

PMC 46 Full Solution Combilaser

Show up on the job with the one tool for all your leveling, aligning, plumbing, and squaring applications. The new Hilti PMC 46 Combilaser coupled with the PMA 78 universal adapter and PMA 20 compact tripod replaces all of the tools and accessories previously needed for plumbing, leveling, aligning and squaring applications. The PMA 78 universal adapter is a four in one solution that replaces wall mounts, ceiling clamps, magnetic brackets, and drywall stands. The innovative Hilti Impact Protection System (IPS) and rubberized drop points increase durability for tough jobsite conditions. The PMC 46 Combilaser – the professional's full solution.

Order Information

Description	Item No.
PMC 46 Combilaser Includes tool, soft pouch, PMW 70 foot, PMA 78 universal adapter, PMA 20 compact tripod, (4) "AA" alkaline batteries and operating instructions in an impact-resistant plastic tool box	00411210
PMA 78 Universal Adapter	00411286
PMA 20 Tripod	00411287
PMA 31 Laser Receiver	00411288
PMA 55 Target Plate	00411290
PMA 74 Magnetic Bracket	00286150
PUA 60 Laser Visibility Glasses	00248988
PMW 70 Foot	00411292

Technical Data	PMC 46
Accuracy	Points: ± 1/8 in at 30 ft (3 mm at 10 m) Beam: ± 1/16" in at 30' (1.5 mm at 10 m)
Self-leveling range	±5°
Settling time	< 3 sec
Laser class	635 nm, class II
IP protection class (except battery compartment)	IP 54
Operating temperature	14° F to + 122° F (-10° C to + 50° C)
Battery life with Alkaline battery	20 h
Dimensions (L x W x H)	4.2 x 2.5 x 3.75 in (107 mm x 65 mm x 96 mm)



Hilti. Outperform. Outlast.