

Applications

- Measuring, checking and transferring heights
- Checking levels when pouring concrete
- Checking and adjusting formwork

Outperform

- High quality optics and mechanical assembly for easy, convenient operation
- Automatic compensator for accurate leveling

Outlast

- Rugged and durable
- All weather dependability



Transfer your job to new heights.

POL 10 Optical Level

The new Hilti POL 10 Optical Level has been uniquely designed to tackle any of the elevation or alignment tasks required on most construction jobsites.

Built with Hilti's high standard of quality, the POL 10 stands up to the toughest demands of your project. Accurate compensators and crystal clear optics provide sharp images even when reading the staff at long distances.

Transfer your jobs to new heights with the quick and easy Hilti POL 10 Optical Level.



*Some limitations apply. Contact Hilti for details.



Technical Data	POL 10
Height accuracy (single measurement)	±1/8 in @ 100 ft
Magnification of telescopic sight	20x
Shortest target distance	2.1 ft
Setting accuracy of compensator	0.5 arcsec
Sensitivity of circular bubble level	8' / 2 mm
Graduation of circle	360°
Operating temperature range	-4 to 122° F (-20 to 50° C)
Compensator type	air-damping
Dimensions (L x W x H)	7.48 x 5.12 x 5.35 in
Weight	4 lb

Order Information

Description	Package Contents	Item No.
POL 10 Optical Level	Includes tool, plumb bob, adjusting screws, and operating instructions in an impact-resistant plastic tool box	00428300

Accessories

PUA 42 Bubble Level	00428688	PA 962 Leveling Staff	00339671
PUA 43 Leveling Plate	00428690	PA 961 Leveling Staff	00338652
		PUA 20 Tripod	00400934

Hilti. Outperform. Outlast.