

Let's get things straight. PRI 2 Rotating Laser



The new Hilti PRI 2 Rotating Laser delivers pinpoint accuracy for all leveling and aligning applications. At the touch of a button, the tool self levels and includes a shock indicator warning that lets the user know if the tool has been knocked out of level. The included PRA 2 remote control allows the user to change rotating speeds, create a working laser line, align the beam and move it 360°.

Ordering Information

Item No.	Description
331411	PRI 2 Rotating Laser Includes tool, PRA 2 remote control, PRA 51 target plate, (2) "D" alkaline batteries and operating instructions in an impact resistant plastic tool box
3427904	PRI 2 Interior Kit Includes tool, PRA 71 wall mount bracket, PRA 2 remote control, PRA 51 target plate, (2) "D" alkaline batteries and operating instructions in an impact resistant plastic tool box
3428196	PRI 2 Interior Kit Rechargeable Includes tool, PRA 71 wall mount bracket, PRA 2 remote control, PRA 51 target plate, (2) "D" alkaline batteries, PRA 82 battery pack, PUA 80 battery charger and operating instructions in an impact resistant plastic tool box
3427905	PRI 2 Deluxe Kit Includes tool, PUA 32 tripod, PRA 22 laser receiver, PRA 2 remote control, PRA 51 target plate, (2) "D" alkaline batteries and operating instructions in an impact resistant plastic tool box
233904	PUA 32 Crank Tripod
331419	PRA 22 Laser Receiver

Technical Data

Accuracy	± 1/8 in. at 100 ft (± 1.0 mm at 10 m)
Range	Up to 100 ft (30 m) without a receiver 7 ft - 500 ft (2-150 m) radius with PRA 22 laser receiver
Function	For horizontal or vertical alignment, setting slopes and laying out right angles
Self-leveling range	+/- 5°
Laser class	635 nm, Class 3a/IIIa (IEC 825-1; FDA 21 CFR 1040)
Protection class	IP 54
Power supply	2 "D" alkaline batteries or optional rechargeable battery pack
Battery life	50 hours with alkaline batteries 40 hours with rechargeable battery pack
Operating temperature	-4° F to 122°F (-20°C to 50°C)
Dimensions (LxWxH)	7.4x7.4x7.6 in. (188x188x194 mm)
Weight	3.5 lb (1.55 kg)

Applications

- Horizontal rotating for hanging suspended ceilings, cable trays and leveling concrete pours
- Vertical rotating for laying out drywall track, pipes, transferring points from floors to ceilings and aligning anchors and rebar
- Slope capability for inclined garage, parking area, handicapped ramps and handrails

Outperform

- Fully automatic horizontal and vertical leveling
- 360° remote control use
- Out of level indicator reduces errors

Outlast

- 4 handle Hilti design for added tool protection and easy of handling
- Optional rechargeable battery back for hours of continued use



Hilti. Outperform. Outlast.