





KCM-MD-CB  $\frac{3}{16}'' - \frac{7}{8}''$

KCM-MD-CB  $\frac{3}{16}'' - 1\frac{1}{8}''$



Anchor Type	Configuration	Item Name	Thread Configurations	Drilling Hole Size	Recommended Combo Bit
KCM-MD (Kwik Cast Multi-thread for Metal Deck)	Short Plate	KCM-MD S $\frac{1}{4}'' + \frac{3}{8}''$	$\frac{1}{4}'' + \frac{3}{8}''$	$\frac{9}{16}''$	KCM-MD-CB $\frac{3}{16}'' - \frac{7}{8}''$
		KCM-MD S $\frac{3}{8}'' + \frac{1}{2}''$	$\frac{3}{8}'' + \frac{1}{2}''$	$1\frac{1}{16}''$	
		KCM-MD S $\frac{1}{4}'' + \frac{3}{8}'' + \frac{1}{2}''$	$\frac{1}{4}'' + \frac{3}{8}'' + \frac{1}{2}''$	$1\frac{1}{16}''$	
		KCM-MD S $\frac{3}{8}'' + \frac{1}{2}'' + \frac{5}{8}''$	$\frac{3}{8}'' + \frac{1}{2}'' + \frac{5}{8}''$	$1\frac{3}{16}''$	
		KCM-MD S $\frac{5}{8}'' + \frac{3}{4}''$	$\frac{5}{8}'' + \frac{3}{4}''$	$1\frac{5}{16}''$	KCM-MD-CB $\frac{3}{16}'' - 1\frac{1}{8}''$
	Long Plate	KCM-MD L $\frac{1}{4}'' + \frac{3}{8}''$	$\frac{1}{4}'' + \frac{3}{8}''$	$\frac{1}{2}''$	KCM-MD-CB $\frac{3}{16}'' - \frac{7}{8}''$
		KCM-MD L $\frac{3}{8}'' + \frac{1}{2}''$	$\frac{3}{8}'' + \frac{1}{2}''$	$\frac{5}{8}''$	
		KCM-MD L $\frac{1}{4}'' + \frac{3}{8}'' + \frac{1}{2}''$	$\frac{1}{4}'' + \frac{3}{8}'' + \frac{1}{2}''$	$\frac{5}{8}''$	
		KCM-MD L $\frac{3}{8}'' + \frac{1}{2}'' + \frac{5}{8}''$	$\frac{3}{8}'' + \frac{1}{2}'' + \frac{5}{8}''$	$\frac{3}{4}''$	KCM-MD-CB $\frac{3}{16}'' - 1\frac{1}{8}''$
		KCM-MD L $\frac{5}{8}'' + \frac{3}{4}''$	$\frac{5}{8}'' + \frac{3}{4}''$	$\frac{7}{8}''$	
KCC-MD (Kwik Cast Connect for Metal Deck)	Short Plate	KCC-MD S $\frac{3}{8}''$	$\frac{3}{8}''$	$1\frac{1}{16}''$	KCM-MD-CB $\frac{3}{16}'' - \frac{7}{8}''$
		KCC-MD S $\frac{1}{2}''$	$\frac{1}{2}''$	$1\frac{3}{16}''$	
	Long Plate	KCC-MD L $\frac{3}{8}''$	$\frac{3}{8}''$	$\frac{5}{8}''$	KCM-MD-CB $\frac{3}{16}'' - 1\frac{1}{8}''$
		KCC-MD L $\frac{1}{2}''$	$\frac{1}{2}''$	$\frac{3}{4}''$	

