

A 360° difference.

PR 2-HS Rotating Laser

Featuring a shock-absorbing casing, the Hilti PR 2-HS Rotating Laser is built to withstand the harshest jobsite conditions. Simple function buttons make this tool incredibly user friendly, and Hilti Pulse Power technology allows for highly reliable readings, even in bright light. Whether setting slopes, transferring heights or leveling, the Hilti PR 2-HS Rotating Laser is the right tool for your job.



HILTI 2 Years
LIFETIME SERVICE™ NO COSTS
 Lifetime REPAIR COST LIMIT Lifetime MANUFACTURERS WARRANTY

*Some limitations apply. Contact Hilti for details.

HILTI
FLEET MANAGEMENT

HILTI
CALIBRATION SERVICE

PULSE III POWER

Applications

- Checking and transferring heights
- Leveling and adjusting formwork
- Checking levels when pouring concrete
- Setting slopes (with optional adapter)

Outperform

- Simple and easy to use
- Best-in-class leveling time
- Drop-resistant from standard working height

Outlast

- Shock absorbent casing
- Resistant to water and dust in typical jobsite conditions
- No-Cost Coverage for 2 years with Hilti Lifetime Service









| Technical Data | PR 2-HS |
|-------------------------------------|----------------------------------------------------|
| Accuracy at 75° F (24° C) | ± 0.02 inch at 32.8 ft (± 0.5 mm at 10 m) |
| Operating range with laser receiver | Diameter: 6 ft – 2000 ft (2 – 600 m) |
| Battery life at 73° F (23° C) | Li-Ion rechargeable (tool): > 30 hours |
| Laser class | 635 nm, class 2 (IEC 825-1), class II (FDA 21 CFR) |
| Protection class | IP 66 as per IEC 60529 |
| Max operating temperature | 122° F (50° C) |

Order Information

| Description | Package Contents | Item No. |
|----------------------------|------------------------------------------------------------------------------------------------------------------------------------|----------|
| PR 2-HS Rotating Laser | Includes tool, li-ion battery, charger, laser-receiver with holder, and operating instructions in an impact-resistant plastic case | 02071034 |
| PR 2-HS with Slope Adapter | Includes tool with its components and PRA 79 slope adapter | 03505460 |
| PR 2-HS Contractor Kit | Includes tool with its components, PRA 79 slope adapter and PUA 20 tripod | 03505462 |

Accessories

| Description | Item No. |
|-----------------------------------------------------------------------------------------------------------------------|----------|
| PRA 79 Slope Adapter  | 02071083 |
| PUA 20 Tripod  | 00400934 |
| PA 961 Leveling Staff  | 00338652 |
| PUA 40 Tripod Bag  | 00377847 |
| PUA 60 Laser Visibility Glasses  | 00284988 |
| PUA 41 Tripod Star  | 00435444 |

Hilti. Outperform. Outlast.