



NUN 54-22

CU-type dies



NUN 54-22 IE-A22 with jaw NCR J SU and NCR SU CU-type dies selection

Dies for copper connectors				Number of crimps per connector ¹					
Type	Item no.	Wire size	Color code	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B
NCR SU CU 8	2183601	8 AWG	Red	1	1	1	1	1	1
NCR SU CU 6	2183602	6 AWG	Blue						
NCR SU CU 4	2183603	4 AWG	Gray						
NCR SU CU 2	2183604	2 AWG	Brown						
NCR SU CU 1	2183605	1 AWG	Green						
NCR SU CU 1/0	2183606	1/0 AWG	Pink						
NCR SU CU 2/0	2183607	2/0 AWG	Black	2	2	2	2	2	2
NCR SU CU 3/0	2183608	3/0 AWG	Orange						
NCR SU CU 4/0	2183609	4/0 AWG	Purple						
NCR SU CU 250	2183650	250 MCM	Yellow						
NCR SU CU 300	2183651	300 MCM	White						
NCR SU CU 350	2183652	350 MCM	Red						
NCR SU CU 400	2183653	400 MCM	Blue						
NCR SU CU 500	2183654	500 MCM	Brown						
NCR SU CU 600	2183655	600 MCM	Green						

¹ Use the number of crimps listed in this column instead of the number provided with the connector

When used with NCR SU CU-type dies, the tool (NUN 54-22 IE-A22 with the crimping jaw NCR J SU) is cULus classified for use with the following connector brands.

Connector type	Barrel type	Anderson	Blackburn®	Burndy	ILSCO	Panduit	T&B
Copper Splice	Short	VHSS	CSP	YS-LI ²	CT	SCSS/SCS	54504-54518
	Long	VHSS	CU	YS ²	CTL	SCL/SCH	54804-54818
Copper Lug	Short	VHCS	CTL-2/CTL	YA-2LN/YA-L/YA-2L	CRA/CRB	LCAS/LCA LCD	54104-54118 54204-54218
	Long	VHCL	CTL-L/LCN	YA-2N	CLN/CLW CRA-L/CRB-L CRA-2L/CRB-2L	LCB/LAB	54930BE-54918BE 548508E-54876BE

² 8 AWG to 350 MCM with Burndy copper-splices

