



VFXT.EX2709 Hangers, Pipe

[Page Bottom](#)

Hangers, Pipe

[See General Information for Hangers, Pipe](#)

HILTI INC

5400 S 122ND EAST AVE
TULSA, OK 74146 USA

EX2709

Pipe hangers

Model	Hanger Type	Rod Size	NPS*	Comments
MP-SP	Band Hanger	10 mm	Up to 4	—
MP-SP	Band Hanger	12 mm	133 mm through 6	—
MP-SP	Band Hanger	16 mm	8	—
HCI-WF	Cast-in-place Concrete Insert	3/8 in.	Up to 4	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-WF	Cast-in-place Concrete Insert	1/2 in.	Up to 8	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-WF	Cast-in-place Concrete Insert	5/8 in.	Up to 8	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-WF	Cast-in-place Concrete Insert	3/4 in.	Up to 8	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-MD	Cast-in-place Concrete Insert	3/8 in.	Up to 4	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-MD	Cast-in-place Concrete Insert	1/2 in.	5 through 8	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-MD	Cast-in-place Concrete Insert	5/8 in.	10, 12	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HCI-MD	Cast-in-place Concrete Insert	3/4 in.	12	Intended for use in concrete w/ a minimum compressive strength of 3000 psi. Also suitable for air-handling spaces
HDI 3/8	Drop-in Anchor	3/8 in.	Up to 4	—
HDI 1/2	Drop-in Anchor	1/2 in.	Up to 8	—
HDI 5/8	Drop-in Anchor	5/8 in.	10, 12	—
HDI 3/4	Drop-in Anchor	3/4 in.	12	—
HDI-L 3/8	Drop-in Anchor	3/8 in.	Up to 4	—
HDI-L 1/2	Drop-in Anchor	1/2 in.	Up to 8	—
HDI+	Drop-in Anchor	3/8 in.	Up to 4	—

HDI-L+	Drop-in Anchor	3/8 in.	Up to 4	—
HDI+	Drop-in Anchor	1/2 in.	Up to 8	—
HDI-L+	Drop-in Anchor	1/2 in.	Up to 8	—
HDV 3/8	Drop-in Anchor	3/8 in.	Up to 4	—
HDV 1/2	Drop-in Anchor	1/2 in.	Up to 8	—
Kwik Bolt 3 3/8	Expansion Anchor Wedge	3/8 in.	Up to 4	—
Kwik Bolt 3 1/2	Expansion Anchor Wedge	1/2 in.	5 through 8	—
Kwik Bolt 3 5/8	Expansion Anchor Wedge	5/8 in.	10, 12	—
Kwik Bolt 3 3/4	Expansion Anchor Wedge	3/4 in.	12	—
Kwik Bolt TZ 3/8	Expansion Anchor Wedge	3/8 in.	Up to 4	—
Kwik Bolt TZ 1/2	Expansion Anchor Wedge	1/2 in.	5 through 8	—
Kwik Bolt TZ 5/8	Expansion Anchor Wedge	5/8 in.	10, 12	—
Kwik Bolt TZ 3/4	Expansion Anchor Wedge	3/4 in.	12	—
KBV 3/8	Expansion Anchor Wedge	3/8 in.	Up to 4	—
KBV 1/2	Expansion Anchor Wedge	1/2 in.	5 through 8	—
KBV 5/8	Expansion Anchor Wedge	5/8 in.	10,12	—
KBV 3/4	Expansion Anchor Wedge	3/4 in.	12	—
MP-MS	Pipe Clamp	10 mm	1/2 through 3	—
MP-MS	Pipe Clamp	12 mm	101.6 mm through 6	—
MF-TSH	Trapezoidal Bracket	10 mm	3/4, 1	—
00257366	Universal Beam Clamp	3/8 in.	Up to 4	—
00306600	Universal Beam Clamp	3/8 in.	Up to 4	—
00257367	Universal Beam Clamp	1/2 in.	Up to 8	—
00306601	Universal Beam Clamp	1/2 in.	Up to 8	—
00306602	Universal Beam Clamp	3/8 in.	Up to 4	—
00306603	Universal Beam Clamp	1/2 in.	Up to 8	—
OES	Offset Eyelet	3/8 in.	Up to 4	—

ES	Eyelet	3/8 in.	Up to 4	—
SDC-EG	Clevis Hanger	5/8 in.	4, 5	—
SDC-EG	Clevis Hanger	3/4 in.	6, 8	—
SDC-EG	Clevis Hanger	1/2 in.	2-1/2, 3, 3-1/2	—
BC	Universal Beam Clamp	1/2 in.	Up to 8	—
BC	Universal Beam Clamp	5/8 in.	Up to 10	—
BC	Universal Beam Clamp	3/4 in.	Up to 10	—
LH	Band Hanger	1/2 in.	8	EG, HD, FL

* NPS = Nominal pipe size

EG - indicates electro-galvanized

FL - indicates felt-lined over EG

HD - indicates hot-dipped

Last Updated on 2013-11-27

[Questions?](#)

[Print this page](#)

[Terms of Use](#)

[Page Top](#)

© 2014 UL LLC

When the UL Leaf Mark is on the product, or when the word "Environment" is included in the UL Mark, please search the [UL Environment database](#) for additional information regarding this product's certification.

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2014 UL LLC".