

# METALWORKING WITH MOBILITY

## Cordless Die grinder GDG 6-A22

Whether you're deburring and beveling or grinding and polishing, Hilti's new cordless die grinder GDG A-22 has you covered.



With innovative, compact design and a powerful, brushless motor, it offers the ability to work in tight spaces while freeing you from the trip hazard of cords and hoses.

The GDG 6-A22 is fully compatible with all of Hilti's 22V batteries and is the perfect addition to your tool crib with a variable speed dial, making it suitable for different metal types. Compatible with industry standard 1/4" wheels, burrs, blades, and brushes, it provides the most flexibility in the hardest to reach spaces.

## APPLICATIONS AND ADVANTAGES

### Applications

- Industrial metal fabrication — rough material removal, removing welds, enlarging and making holes, and preparing pipes for welding
- On-site metalwork — cleaning surfaces, welds and pipes, removing rust, deburring, polishing, burnishing, and other fine finishing

### Advantages

- Built for higher performance — equipped with high torque and a brushless motor for optimal performance
- Variable speed — adjustable from 10,000-25,000 rpm to select the best balance of high-speed material removal and fine finishing
- Brushless motor — maximize power output while helping reduce the maintenance required compared to corded or air die grinders
- Designed for efficiency — engineered to help remove more metal per battery charge and per minute, helping you to get more done in less time
- Advanced ergonomics — lock-on switch and well-balanced tool body give you the comfort and control needed for precise metalwork

### Order information

Description	Item number
GDG 6-A22 die grinder (tool body)	2257601

### Accessories

Description	Item number
1/4" Collet	2280320
Collet nut	2278641



we want to hear from you



Tool warranty. Some limitations apply. Contact Hilti for details.