




# THE CHOICE IS CLEAR

Whatever the job, whatever the budget.

Hilti has what it takes to get the job done. Whether you need ultimate performance for a demanding situation or a reliable product for everyday use, the choice is clear.

## THREE LINES OF CONSUMABLES — CHOOSE THE LINE TO MEET YOUR NEEDS

Three colors, three performance levels, three price points —all under one brand that delivers quality you can rely on.

 <b>ULTIMATE</b>	 <b>PREMIUM</b>	 <b>STANDARD</b>
<b>Ultimate performance for demanding applications</b> <ul style="list-style-type: none"> <li>Highest overall productivity and safety benefits</li> <li>Highest reliability in toughest conditions</li> </ul>	<b>Premium performance for a wide range of applications</b> <ul style="list-style-type: none"> <li>High productivity through Hilti system solutions</li> <li>Impressive versatility and reliability</li> </ul>	<b>Hilti quality at an economical price</b>












# FROM GRIND TO FINISH — ABRASIVES FOR ANY JOB

## Expanded Abrasive Portfolio

Our expanded abrasive portfolio has you covered for stock removal, beveling, weld removal, blending, polishing, and more. The most complete abrasive portfolio we've ever offered was developed with productivity and high performance in mind. Hilti's new multiline solutions allow you to choose the level of performance based on your needs.

Choose between Ultimate SPX for fast material removal, long life and exceptional finish quality, Premium SP for a great balance of speed and durability, or Standard P for convenience in grinding. All lines developed for use with stainless and carbon steel. Whatever you need, we have the metal grinding and finishing abrasive solutions to get the job done.

### Meet the new abrasives:

	BLENDING			FINISHING/POLISHING
	Flap disc	Fiber disc	Coated Belts	Non-woven belts
 <b>ULTIMATE</b> Ultimate performance for demanding applications				
 <b>PREMIUM</b> Premium performance for a wide range of applications				
 <b>STANDARD</b> Hilti quality at economical price				

More Abrasive Portfolio information on the next page 



we want to hear from you 



## UPGRADED FLAP AND FIBER DISCS WITH NEW AND IMPROVED SP AND SPX PORTFOLIO

Designed for comfortable use in more aggressive cutting and grinding applications, while also allowing for blending and finishing work for when materials needs to be painted, primed, or powder-coated



Great for cordless and corded grinders


## ELEVATE METAL FINISHING WITH COATED AND NON-WOVEN ABRASIVE BELTS

Get longer life and stronger performance for rough grinding and polishing with our premium self-sharpening grains.



Belts fit new finishing tools as well as competitors tools!

File belt  
Tube file belt  
Burnisher




## APPLICATIONS AND ADVANTAGES

- Improved lifetime — 47% over previous portfolio
- Improved material removal speed
- Expanded portfolio — more grit and size options now available
- New trimmable HUB option available for increased productivity
- 7/8" and 5/8"-11 threaded hub options available
- Fiberglass back option available



Flap Disc						
Dia.	Grit	Arbor	Grade	Qty	Item number	
					Flat	Convex
<b>Fiberglass</b>						
4.5"	36-40	7/8"	■	10	2243317	2243333
4.5"	60	7/8"	■	10	2243311	2243325
4.5"	80	7/8"	■	10	2243361	2243287
5"	36-40	7/8"	■	10	2243270	2243301
5"	60	7/8"	■	10	2243373	2243295
5"	80	7/8"	■	10	2243261	2243298
7"	36-40	7/8"	■	10	2243275	2243354
4.5"	36-40	7/8"	■	10	2243316	2243290
4.5"	60	7/8"	■	10	2243357	2243323
4.5"	80	7/8"	■	10	2243359	2243327
4.5"	120	7/8"	■	10	2243365	2243288
5"	36-40	7/8"	■	10	2243268	2243299
5"	60	7/8"	■	10	2243371	2243293
5"	80	7/8"	■	10	2243259	2243337
5"	120	7/8"	■	10	2243265	2243342
7"	36-40	7/8"	■	10	2243274	2243353
<b>Plastic Trimmable</b>						
4.5"	36-40	5/8"-11	■	10	2243369	2243334
4.5"	60	5/8"-11	■	10	2243313	2243285
4.5"	80	5/8"-11	■	10	2243363	2243330
5"	36-40	5/8"-11	■	10	2243272	2243303
5"	60	5/8"-11	■	10	2243375	2243336
5"	80	5/8"-11	■	10	2243263	2243340
4.5"	36-40	5/8"-11	■	10	2243370	2243335
4.5"	60	5/8"-11	■	10	2243314	2243286
4.5"	80	5/8"-11	■	10	2243364	2243331
4.5"	120	5/8"-11	■	10	2243315	2243289
5"	36-40	5/8"-11	■	10	2243273	2243304
5"	60	5/8"-11	■	10	2243258	2243297
5"	80	5/8"-11	■	10	2243264	2243341
5"	120	5/8"-11	■	10	2243267	2243344



## APPLICATIONS AND ADVANTAGES

- SPX has an added conditioner which allows it to stay cooler longer, great for stainless steel
- SP recommended for carbon steel and edge-work
- More flexible than a hard bonded disc, great for flatwork
- P — Hilti quality at an economical price



Fiber Disc					
Dia.	Grit	Grade	Qty	Item number	
				4.5"	36-40
5"	36-40	■	25	2243216	2243253
4.5"	60	■	25	2243220	2243255
5"	60	■	25	2243240	2243222
4.5"	80	■	25	2243214	2243249
5"	80	■	25	2243238	2243221
4.5"	120	■	25	2243208	2243219
5"	120	■	25	2243209	2243217
7"	36-40	■	25	2243226	2243229
4.5"	36-40	■	25	2243212	2243212
5"	36-40	■	25	2243247	2243239
4.5"	60	■	25	2243223	2243210
5"	60	■	25	2243215	2243211
4.5"	80	■	25	2243211	2243213

## Back Pads

Diameter	Qty	Item number
4.5" med	1	2243193
5" med	1	2243197
7" hard	1	2243183
4.5" hard	1	2243176
5" hard	1	2243178

## APPLICATIONS AND ADVANTAGES

### SPX

- SPX 20% better life + 25% greater speed versus SP
- Up to 50% better lifetime than common brands
- Excellent finish quality versus competition

### SP

- Up to 30% better lifetime versus common brands
- Up to 35% better speed versus common brands
- Great value for the money

METAL WORKING ABRASIVES		
	Coated Belts	Non-woven belts
<b>SPX ULTIMATE</b>		
<b>SP PREMIUM</b>		

## File belt

Dimension (mm)	Grit	Grade	Qty	Item number
<b>Rough Grinding</b>				
13 x 457	60	■	20	2243161
13 x 457	80	■	20	2243162
9 x 457	40	■	20	2243008
9 x 457	60	■	20	2243009
9 x 457	80	■	20	2243150
9 x 457	120	■	20	2243151
13 x 457	60	■	20	2243158
13 x 457	80	■	20	2243159
13 x 457	120	■	20	2243160
30 x 457	40	■	20	2243152
30 x 457	60	■	20	2243153
30 x 457	80	■	20	2243156
30 x 457	120	■	20	2243157
<b>Finishing / Polishing</b>				
13 x 457	Coarse	■	10	2243381
13 x 457	Medium	■	10	2243382
13 x 457	V-Fine	■	10	2243384
13 x 457	Fine	■	10	2243389

## Accessories

Description	Dimension (mm)	Qty	Item number
Crowned arm	25 x 9	1	2242232
Small arm	20 x 30	1	2242233
Large arm	30 x 30	1	2242234
Pointed arm	25 x 9	1	2242231
Spacing ring set		1	2242230
Roller set		1	2242909

## Tube belt

Dimension (mm)	Grit	Grade	Qty	Item number
<b>Rough Grinding</b>				
40 x 760	60	■	20	2243154
40 x 760	80	■	20	2243155
40 x 760	40	■	20	2243163
40 x 760	60	■	20	2243164
40 x 760	80	■	20	2243165
40 x 760	120	■	20	2243166
<b>Finishing / Polishing</b>				
40 x 760	Coarse	■	10	2243385
40 x 760	Medium	■	10	2243386
40 x 760	V-Fine	■	10	2243388
40 x 760	Fine	■	10	2243390
40 x 760	Felt	■	10	2243397

## Accessories

Description	Qty	Item number
Interchangeable roller set	1	2242017
Guard plate	1	2242908

## Burnisher

Dimension (mm)	Grit	Grade	Qty	Item number
<b>Rough Grinding</b>				
100 mm	60	■	20	2243171
100 mm	80	■	20	2243172
100 mm	40	■	20	2243167
100 mm	60	■	20	2243168
100 mm	80	■	20	2243169
100 mm	120	■	20	2243170
100 mm	40	■	1	2243379
100 mm	60	■	1	2243377
100 mm	80	■	1	2243378
100 mm	240	■	1	2243376
<b>Finishing / Polishing</b>				
100 mm	Felt	■	10	2243392
100 mm	V-Fine	■	10	2243410
100 mm	Coarse	■	10	2243411
100 mm	Medium	■	10	2243412
100 mm	Fine	■	10	2243413
100 mm	V-Fine	■	1	2243414
100 mm	Medium	■	1	2243416

## Accessories

Description	Qty	Item number
Dust extr. Hood	1	2240615
Inflatable expansion roller	1	2242019
Protective cover	1	2240612
Air pump	1	2240613
Parallel guide	1	2240616