

5.0 Installation System Hangers

5.3 Split rings

Split rings — electro galvanized

Product Features

- For suspending uninsulated stationary pipe. Allows for piping runs close to ceilings or walls

Material Specifications


Material	Malleable iron body, carbon steel rivet and bolt
Finish	Electro-galvanized
Conforms with	<ul style="list-style-type: none"> • Federal specification WW-H-171 (Type 25) • Manufacturers Standardization Society MSS-SP-58 (Type 12)
Installation	Install in accordance with ANSI/MSS-SP-58



Ordering Information / Technical Data

Description	Weight/ Piece (lb)	Pipe Size	Rod Size (RS)	Center Line (CL)	Min. Rod Insertion (MR)	Qty	Item No.	Maximum Allowable Load (lb) ¹
SR-EG 1/2"	0.18	1/2"	3/8"	16/16"	3/8"	100	306630	180
SR-EG 3/4"	0.22	3/4"	3/8"	1-5/16"	3/8"	100	306631	180
SR-EG 1"	0.23	1"	3/8"	1-1/16"	3/8"	100	306632	180
SR-EG 1-1/2"	0.34	1-1/2"	3/8"	1-3/16"	3/8"	50	306633	180
SR-EG 2"	0.37	2"	3/8"	1-7/16"	3/8"	50	306634	180

¹ Based on a safety factor of 3.5



Split Rings — Copper

Product Features

- For suspending uninsulated stationary copper tubing. Allows for piping runs close to ceilings or walls

Material Specifications

Material	Malleable iron body, carbon steel rivet and bolt with copper electroplate finish
Finish	Copper
Conforms with	<ul style="list-style-type: none"> • Federal specification WW-H-171 (Type 25) • Manufacturers Standardization Society MSS-SP-58 (Type 12)
Installation	Install in accordance with ANSI/MSS-SP-58

Note: This pipe support is not designed for corrosion or electrolysis resistance. Copper plating is for identification purposes only



Ordering Information / Technical Data

Description	Weight/ Piece (lb)	Pipe Size	Rod Size (RS)	Center Line (CL)	Min. Rod Insertion (MR)	Qty	Item No.	Maximum Allowable Load (lb) ¹
Copper SR 1/2"	0.18	1/2"	3/8"	11/16"	3/8"	100	306623	180
Copper SR 3/4"	0.22	3/4"	3/8"	13/16"	3/8"	100	306624	180
Copper SR 1"	0.23	1"	3/8"	15/16"	3/8"	100	306625	180
Copper SR 1-1/4"	0.25	1-1/4"	3/8"	1-1/16"	3/8"	100	306626	180
Copper SR 1-1/2"	0.34	1-1/2"	3/8"	1-3/16"	3/8"	100	306627	180
Copper SR 2"	0.37	2"	3/8"	1-7/16"	3/8"	50	306628	180

¹ Based on a safety factor of 3.5

