

## 4.3 Accessories


### MQZ-L Base plates

#### Product Features

- Used as heavy plate washer for strut


#### Material Specifications

<b>Material</b>	Carbon steel Stainless Steel 1.4404 (316 L)
<b>Material thickness</b>	3/16" (4 mm)
<b>Finish</b>	Hot-dipped galvanized, min. 2.2 mil (55 µm), DIN EN ISO 1461, ASTM A153 Electro-galvanized



#### Ordering Information

Description	For Thread	Weight/Piece (lb)	Qty	Item No.
<b>MQZ-L 3/8</b>	3/8	0.203	20	370632
<b>MQZ-L 3/8-F (HDG)</b>	3/8	0.194	20	304200
<b>MQZ-L 3/8-R (SS316)</b>	3/8	0.194	20	304076
<b>MQZ-L 1/2</b>	1/2	0.185	20	370633
<b>MQZ-L 1/2-F (HDG)</b>	1/2	0.185	20	304201
<b>MQZ-L 1/2-R (SS316)</b>	1/2	0.185	20	304077
<b>MQZ-L 5/8</b>	5/8	0.176 (80)	20	370634




### MQZ-SS Strut Tie

#### Product Features

- For user-assembled back to back struts

#### Material Specifications

<b>Finish</b>	Electro-galvanized
---------------	--------------------



Note: strut side cut away to show fastener

#### Ordering Information

Description	Width Across Flats (mm)	Weight/Piece (lb)	Qty	Item No.
<b>MQZ-SS Locking device</b> — For user-assembled B2B strut, use 13 mm socket to set	13 mm	0.006	40	369691

#### Technical Data — Allowable Loads<sup>1,2</sup>

<b>F<sub>y</sub></b>	675 lb (3.0 kN)
<b>F<sub>x</sub></b>	1125 lb (5.0 kN)
<b>Tightening torque, M<sub>p</sub></b>	15ft-lb (20 Nm)

<sup>1</sup> Based on a safety factor of 2.2

<sup>2</sup> F<sub>y</sub> + F<sub>x</sub>

