

## Contents

Stainless Steel Stud with Sealing Washer .....	2
• S-BT-MR M8/7 SN 6 HL .....	2
• S-BT-MR M8/15 SN 6 HL .....	2
• S-BT-MR M10/15 SN 6 HL .....	2
• S-BT-MR W10/15 SN 6 HL .....	2
• S-BT-MR M8/7 SN 6 HL AL .....	2
• S-BT-MR M8/15 SN 6 HL AL .....	2
• S-BT-MR M10/15 SN 6 HL AL .....	2
• S-BT-MR W10/15 SN 6 HL AL .....	3
• S-BT-GR M8/7 SN 6 HL .....	3
• S-BT-GR M8/7 SN 6 HL AL .....	3
• S-BT-ER M8/15 SN 6 HL.....	3
• S-BT-ER M10/15 SN 6 HL.....	3
• S-BT-ER W10/15 SN 6 HL .....	3
• S-BT-ER M10 HC 120 HL .....	4
• S-BT-ER W10 HC 4/0 HL .....	4
Carbon Steel Stud with Sealing Washer .....	4
• S-BT-MF M8/7 AN 6 HL .....	4
• S-BT-MF M8/15 AN 6 HL .....	4
• S-BT-MF M10/15 AN 6 HL .....	4
• S-BT-MF W10/15 AN 6 HL.....	5
• S-BT-MF MT M10/15 AN 6 HL.....	5
• S-BT-MF MT W10/15 AN 6 HL.....	5
• S-BT-GF M8/7 AN 6 HL.....	5
• S-BT-EF M8/15 AN 6 HL.....	5
• S-BT-EF M10/15 AN 6 HL .....	5
• S-BT-EF W10/15 AN 6 HL .....	5
• S-BT-EF M10 HC 120 HL .....	6
• S-BT-EF W10 HC 4/0 HL.....	6

## Stainless Steel Stud with Sealing Washer

- **S-BT-MR M8/7 SN 6 HL**

S-BT-MR M8/7 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 23.2mm [0.91"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185.

- **S-BT-MR M8/15 SN 6 HL**

S-BT-MR M8/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR M10/15 SN 6 HL**

S-BT-MR M10/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR W10/15 SN 6 HL**

S-BT-MR W10/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size W10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR M8/7 SN 6 HL AL**

S-BT-MR M8/7 SN 6 HL AL screw-in threaded studs are fastened to support aluminum with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 23.2mm [0.91"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR M8/15 SN 6 HL AL**

S-BT-MR M8/15 SN 6 HL AL screw-in threaded studs are fastened to support aluminum with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR M10/15 SN 6 HL AL**

S-BT-MR M10/15 SN 6 HL AL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for

corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MR W10/15 SN 6 HL AL**

S-BT-MR M8/7 SN 6 HL AL screw-in threaded studs are fastened to support aluminum with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size W10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-GR M8/7 SN 6 HL**

S-BT-GR M8/7 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 23.2mm [0.91"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-GR M8/7 SN 6 HL AL**

S-BT-GR M8/7 SN 6 HL AL screw-in threaded studs are fastened to support aluminum with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 23.2mm [0.91"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-ER M8/15 SN 6 HL**

S-BT-ER M8/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M8 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-ER M10/15 SN 6 HL**

S-BT-ER M10/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-ER W10/15 SN 6 HL**

S-BT-ER W10/15 SN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size W10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL)

Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-ER M10 HC 120 HL**

S-BT-ER M10 HC 120 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size M10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-ER W10 HC 4/0 HL**

S-BT-ER W10 HC 4/0 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Stainless Steel 1.4462 (A4), with a thread size W10 and 33.9mm [1.33"] length. Stainless steel and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

## Carbon Steel Stud with Sealing Washer

- **S-BT-MF M8/7 AN 6 HL**

S-BT-MF M8/7 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M8 and 23.2mm [0.91"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MF M8/15 AN 6 HL**

S-BT-MF M8/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M8 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MF M10/15 AN 6 HL**

S-BT-MF M10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MF W10/15 AN 6 HL**

S-BT-MF W10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of W10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MF MT M10/15 AN 6 HL**

S-BT-MF MT M10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-MF MT W10/15 AN 6 HL**

S-BT-MF MT W10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of W10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-GF M8/7 AN 6 HL**

S-BT-GF M8/7 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M8 and 23.2mm [0.91"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

- **S-BT-EF M8/15 AN 6 HL**

- **S-BT-EF M8/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M8 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).**

S-BT-EF M10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-EF W10/15 AN 6 HL**

S-BT-EF W10/15 AN 6 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of W10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by ICC Evaluation Services, ESR #4185

Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-EF M10 HC 120 HL**

S-BT-EF M10 HC 120 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of M10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).

- **S-BT-EF W10 HC 4/0 HL**

S-BT-EF W10 HC 4/0 HL screw-in threaded studs are fastened to support steel with Hilti cordless drill tools to pre-drill the pilot hole and screw-in the threaded stud. Stud of Carbon steel 1038 (duplex coated), with a thread size of W10 and 33.9mm [1.33"] length. Aluminum and Chloroprene washer for corrosion protection. Type Approval Certificate by DNV, Lloyds Register, RINA, ABS and Bureau Veritas. Evaluation Report by IEC (60947-7-2, 60947-7-1, 62561-1). Underwriters Laboratories (UL) Certificate of Compliance E257069 confirming safety for use as grounding and bonding equipment (Standards UL 467 & CAN/CSA C22.2 No 41-13).