

UL SYSTEM NO. C-AJ-2831

**PLASTIC PIPE THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY**

F-RATING = 3-HR.


T-RATING = 0-HR., 2-1/2-HR., OR 3-HR. (SEE NOTE NO. 3 AND TABLE BELOW)

L-RATING AT AMBIENT = LESS THAN 1 CFM / SQ FT


L-RATING AT 400°F = LESS THAN 1 CFM / SQ FT

CAJ2831d.030723

**BOTTOM VIEW**



**SECTION A-A**



1. CONCRETE FLOOR OR WALL ASSEMBLY (3-HR. FIRE-RATING) :
  - A. LIGHTWEIGHT OR NORMAL WEIGHT CONCRETE FLOOR OR WALL (MINIMUM 4-1/2" THICK).
  - B. ANY UL CLASSIFIED CONCRETE BLOCK WALL.
2. [OPTIONAL- NOT SHOWN] MAXIMUM 7" NOMINAL DIAMETER STEEL PIPE SLEEVE (SCHEDULE 40 OR THINNER) (SEE NOTE NO. 3 BELOW).
3. PENETRATING ITEM MAY BE ONE OF THE FOLLOWING :
  - A. MAXIMUM 6" (160 MM OD) NOMINAL DIAMETER AQUATHERM GREENPIPE POLYPROPYLENE (PP-R) PLASTIC PIPE (SDR 7.4 OR 11) (CLOSED OR VENTED PIPING SYSTEM).
  - B. MAXIMUM 6" (160 MM OD) NOMINAL DIAMETER AQUATHERM BLUEPIPE POLYPROPYLENE (PP-RCT) PLASTIC PIPE (SDR 9 OR 11) (CLOSED OR VENTED PIPING SYSTEM).
  - C. MAXIMUM 6" (160 MM OD) NOMINAL DIAMETER NUPI AMERICAS NIRON POLYPROPYLENE (PP-RCT) PLASTIC PIPE (SDR 7.3, 9, OR 11) (CLOSED OR VENTED PIPING SYSTEM).
  - D. MAXIMUM 6" (160 MM OD) NOMINAL DIAMETER AQUATECHNIK NA FUSION-TECH POLYPROPYLENE (PP-RCT) PLASTIC PIPE (SDR 7.4 OR 11) (CLOSED OR VENTED PIPING SYSTEM).



Hilti Firestop Systems

HILTI, Inc.  
Plano, Texas USA (800) 879-8000

Sheet 1 of 2

Scale 5/32" = 1"

Date Mar. 07, 2023

Drawing No.

**CAJ  
2831d**

*Saving Lives through Innovation and Education*

**PLASTIC PIPE THROUGH CONCRETE FLOOR/WALL OR BLOCK WALL ASSEMBLY**

F-RATING = 3-HR.

T-RATING = 0-HR., 2-1/2-HR., OR 3-HR. (SEE NOTE NO. 3 AND TABLE BELOW)

L-RATING AT AMBIENT = LESS THAN 1 CFM / SQ FT

L-RATING AT 400°F = LESS THAN 1 CFM / SQ FT

CAJ2831d.030723

- E. MAXIMUM 6" (160 MM OD) NOMINAL DIAMETER UPONOR POLYPROPYLENE (PP) PLASTIC PIPE (SDR 9 OR 11) (CLOSED OR VENTED PIPING SYSTEM).
  - F. MAXIMUM 6" (152 MM) NAPSYS-HR PVC HR POLYVINYL CHLORIDE (PVC-HR) PIPE (SCHEDULE 40) (CLOSED OR VENTED PIPING SYSTEM).
  - G. MAXIMUM 6" (152 MM OD) NOMINAL DIAMETER PVC PLASTIC PIPE (SCHEDULE 40) (CLOSED OR VENTED PIPING SYSTEM).
  - H. MAXIMUM 6" (152 MM OD) NOMINAL DIAMETER CPVC PLASTIC PIPE (SCHEDULE 40) (CLOSED PIPING SYSTEM) (SEE TABLE BELOW).
4. [NOT SHOWN] FOR ITEMS 2G AND 2H A MAXIMUM NOMINAL 6" DIAMETER PIPE COUPLING SHALL BE BUTTED AGAINST THE BOTTOM SURFACE OF THE FLOOR ASSEMBLY OR BOTH SURFACES OF A WALL ASSEMBLY.
  5. MINIMUM 2" THICKNESS MINERAL WOOL (MIN. 4 PCF DENSITY) TIGHTLY PACKED, RECESSED TO ACCOMMODATE SEALANT.
  6. MINIMUM 1" DEPTH HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT.
  7. HILTI CP 648E WRAP STRIP (NOMINAL 3/16" THICK X 1-3/4" WIDE) CONTINUOUSLY WRAPPED AROUND THE OUTER CIRCUMFERENCE OF THE PIPE, COVERING FOUR TIMES, WITH ENDS BUTTED AND HELD IN PLACE WITH TAPE. BUTTED ENDS IN SUCCESSIVE LAYER SHALL BE OFFSET. TWO STACKS OF 4 LAYERS SHALL BE INSTALLED AND BUTTED TIGHTLY TO BOTTOM SURFACE OF FLOOR.
  8. FIRST HILTI RETAINING COLLAR SHALL BE WRAPPED AROUND TOP LAYER OF WRAP STRIPS WITH ENDS OVERLAPPING 2" AND SECURED WITH TWO NO. 8 SHEET METAL SCREWS. SECURE EVERY OTHER TAB TO BOTTOM SURFACE OF FLOOR WITH 1-1/4" LONG CONCRETE SCREW ANCHORS AND 1-1/4" WASHERS.
  9. SECOND HILTI RETAINING COLLAR SHALL BE WRAPPED AROUND BOTTOM LAYER OF WRAP STRIPS WITH ENDS OVERLAPPING 2" AND SECURED WITH FOUR NO. 8 SHEET METAL SCREWS. SECURE EVERY OTHER TAB TO FIRST RETAINING COLLAR WITH ONE NO. 8 SHEET METAL SCREW.

| PENETRANT          | T-RATING, HR. | MAX ANNULAR SPACE, IN. | STEEL SLEEVE | COUPLING |
|--------------------|---------------|------------------------|--------------|----------|
| 2A, 2B, 2C, 2D, 2E | 2-1/2         | 3/4"                   | OPTIONAL     | NO       |
| 2F                 | 3             | 1/2"                   | OPTIONAL     | NO       |
| 2G, 2H             | 2-1/2         | 3/8"                   | NO           | REQUIRED |

NOTES : 1. MAXIMUM DIAMETER OF OPENING = 7".  
 2. HILTI CP 648E WRAP STRIP WITH RETAINING COLLAR AND HILTI FS-ONE MAX INTUMESCENT FIRESTOP SEALANT ARE REQUIRED ON EACH SIDE OF A WALL ASSEMBLY.  
 3. T-RATING = 0-HR. WHEN STEEL SLEEVE (ITEM 2) IS USED.



HILTI, Inc.  
 Plano, Texas USA (800) 879-8000

|       |               |
|-------|---------------|
| Sheet | 2 of 2        |
| Scale | -             |
| Date  | Mar. 07, 2023 |

Drawing No.  
**CAJ**  
**2831d**