

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Issue date: 8/16/2023 Revision date: 8/16/2023 Supersedes: 4/5/2023 Version: 3.0

SECTION 1: Identification

1.1. Identification

Product form	Mixture
Name	GC FX 3
Product code	BU Direct Fastening

1.2. Recommended use and restrictions on use

Use of the substance/mixture	Gas can for use exclusively with the Hilti FX 3-A tool. For professional use only
------------------------------	--------------------------------------------------------------------------------------

1.3. Supplier

Supplier Hilti, Inc. Legacy Tower, Suite 1000 7250 Dallas Parkway Plano, TX 75024 USA T +1 9724035800 1-800-879-8000 toll free - F +1 918 254 0522	Department issuing data specification sheet Hilti AG Feldkircherstraße 100 Schaan, 9494 Liechtenstein T +423 234 2111 df-hse@hilti.com
--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

1.4. Emergency telephone number

Emergency number	Emergency contact (24 hours per day) GBK/Infotrac ID 101022 (USA domestic) 1 800 535 5053 or international (001)352 323 3500
------------------	---------------------------------------------------------------------------------------------------------------------------------

SECTION 2: Hazard(s) identification

2.1. Classification of the substance or mixture

GHS-US classification

Gases under pressure : Compressed gas	H280	Contains gas under pressure; may explode if heated.
Full text of H-statements: see section 16		

2.2. GHS Label elements, including precautionary statements

GHS US labelling

Hazard pictograms (GHS US) :



Signal word (GHS US) :

: Warning

Hazard statements (GHS US) :

: H280 - Contains gas under pressure; may explode if heated.

Precautionary statements (GHS US) :

: P251 - Do not pierce or burn, even after use.

P402 - Store in a dry place.

P403 - Store in a well-ventilated place.

P410+P412 - Protect from sunlight. Do not expose to temperatures exceeding 50°C/122°F.

2.3. Other hazards which do not result in classification

Other hazards which do not result in classification : No additional information available.

2.4. Unknown acute toxicity (GHS US)

Not applicable

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

SECTION 3: Composition/information on ingredients

3.1. Substances

Not applicable

3.2. Mixtures

Name	Product identifier	%	GHS-US classification
argon	CAS-No.: 7440-37-1	≥ 80	Press. Gas (Comp.), H280
Carbon dioxide	CAS-No.: 124-38-9	10 – 25	Press. Gas (Liq.), H280

Full text of hazard classes and H-statements : see section 16

SECTION 4: First-aid measures

4.1. Description of first aid measures

First-aid measures general

Asphyxiant in high concentrations. Never give anything by mouth to an unconscious person. If you feel unwell, seek medical advice (show the label where possible).

First-aid measures after inhalation

In high concentrations may cause asphyxiation. Symptoms may include loss of mobility/consciousness. Victim may not be aware of asphyxiation. Remove victim to uncontaminated area wearing self contained breathing apparatus. Keep victim warm and rested. Call a doctor. Apply artificial respiration if breathing stopped. Low concentrations of CO2 cause increased respiration and headache.

First-aid measures after skin contact

Remove affected clothing and wash all exposed skin area with mild soap and water, followed by warm water rinse. Wash skin with plenty of water.

First-aid measures after eye contact

Rinse immediately with plenty of water. Rinse eyes with water as a precaution.

First-aid measures after ingestion

Rinse mouth. Do NOT induce vomiting. Obtain emergency medical attention. Call a poison center or a doctor if you feel unwell.

4.2. Most important symptoms and effects (acute and delayed)

Symptoms/effects

Not expected to present a significant hazard under anticipated conditions of normal use.

Symptoms/effects after inhalation

Respiratory complaints.

4.3. Immediate medical attention and special treatment, if necessary

Treat symptomatically.

SECTION 5: Fire-fighting measures

5.1. Suitable (and unsuitable) extinguishing media

Suitable extinguishing media

The product is non-combustible. Use extinguishing agent suitable for surrounding fire.

5.2. Specific hazards arising from the chemical

Explosion hazard

Contains gas under pressure; may explode if heated.

5.3. Special protective equipment and precautions for fire-fighters

Firefighting instructions

In case of fire: stop leak if safe to do so. Continue water spray from protected position until container stays cool.

Protection during firefighting

Wear recommended personal protective equipment.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

General measures

Evacuate area. Mechanically ventilate the spillage area.

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

6.1.1. For non-emergency personnel

Emergency procedures Evacuate area. Ventilate spillage area.

6.1.2. For emergency responders

Protective equipment Do not attempt to take action without suitable protective equipment. For further information refer to section 8: "Exposure controls/personal protection".

Emergency procedures Ventilate area.

6.2. Environmental precautions

Avoid release to the environment.

6.3. Methods and material for containment and cleaning up

Methods for cleaning up Provide adequate ventilation.

6.4. Reference to other sections

For further information refer to section 8: "Exposure controls/personal protection". For further information refer to section 13.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Precautions for safe handling Ensure good ventilation of the work station. Pressurized container: Do not pierce or burn, even after use. Damaged cylinders should be handled by specialists only. Carefully comply with the instructions for use.

Hygiene measures Do not eat, drink or smoke when using this product. Always wash hands after handling the product.

7.2. Conditions for safe storage, including any incompatibilities

Storage conditions Store at temperatures not exceeding 50 °C. Protect from sunlight. Store in a well-ventilated place. Keep cool. Store in a dry place.

Incompatible products Strong acids. Strong bases. Combustible materials.

Incompatible materials Sources of ignition. Direct sunlight. Heat sources.

Storage temperature -20 – 50 °C

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

GC FX 3	
No additional information available	
Carbon dioxide (124-38-9)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Carbon dioxide
ACGIH OEL TWA [ppm]	5000 ppm
ACGIH OEL STEL [ppm]	30000 ppm
Remark (ACGIH)	TLV® Basis: Asphyxia
Regulatory reference	ACGIH 2023
USA - OSHA - Occupational Exposure Limits	
Local name	Carbon dioxide

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Carbon dioxide (124-38-9)	
OSHA PEL TWA [1]	9000 mg/m ³
OSHA PEL TWA [2]	5000 ppm
Regulatory reference (US-OSHA)	OSHA Annotated Table Z-1

argon (7440-37-1)	
USA - ACGIH - Occupational Exposure Limits	
Local name	Argon
Remark (ACGIH)	TLV® Basis: Simple Asphyxiant
Regulatory reference	ACGIH 2023

8.2. Appropriate engineering controls

Appropriate engineering controls	Ensure good ventilation of the work station. Systems under pressure should be regularly checked for leakages.
Environmental exposure controls	No specific measures are required provided the product is handled in accordance with the general rules of occupational hygiene and safety. Avoid release to the environment.

8.3. Individual protection measures/Personal protective equipment

Personal protective equipment:

Avoid all unnecessary exposure.

Hand protection:		
Not required for normal conditions of use		
Eye protection:		
Safety glasses		
Type	Field of application	Characteristics
Safety glasses		clear
Respiratory protection:		
Keep self contained breathing apparatus readily available for emergency use.		

Personal protective equipment symbol(s):



Thermal hazard protection:

No information available.

Other information:

Do not eat, drink or smoke during use.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

Physical state Gas

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Colour	Colourless
Odour	odourless
Odour threshold	No data available
pH	Not applicable
Melting point	Not applicable
Freezing point	Not applicable
Boiling point	Not applicable
Flash point	Not applicable
Relative evaporation rate (butylacetate=1)	No data available
Flammability (solid, gas)	Non flammable Non flammable.
Vapour pressure	Not available
Vapour pressure at 50°C	Not available
Relative vapour density at 20°C	No data available
Relative density	No data available
Solubility	No data available
Partition coefficient n-octanol/water (Log Pow)	No data available
Auto-ignition temperature	Not applicable
Decomposition temperature	No data available
Viscosity, kinematic	No data available
Viscosity, dynamic	No data available
Explosive limits	No data available
Explosive properties	Not applicable.
Oxidising properties	Not applicable.

9.2. Other information

Gas group	Gases under pressure : Compressed gas
Other properties	Gas/vapour heavier than air. May accumulate in confined spaces, particularly at or below ground level.

SECTION 10: Stability and reactivity

10.1. Reactivity

The product is non-reactive under normal conditions of use, storage and transport.

10.2. Chemical stability

Stable under normal conditions.

10.3. Possibility of hazardous reactions

No dangerous reactions known under normal conditions of use.

10.4. Conditions to avoid

Direct sunlight. Extremely high or low temperatures. Moisture.

10.5. Incompatible materials

No additional information available.

10.6. Hazardous decomposition products

Under normal conditions of storage and use, hazardous decomposition products should not be produced.

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

SECTION 11: Toxicological information

11.1. Information on toxicological effects

Acute toxicity (oral)	Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (dermal)	Not classified (Based on available data, the classification criteria are not met)
Acute toxicity (inhalation)	Not classified (Based on available data, the classification criteria are not met)
Skin corrosion/irritation	Not classified (Based on available data, the classification criteria are not met) pH: Not applicable
Serious eye damage/irritation	Not classified (Based on available data, the classification criteria are not met) pH: Not applicable
Respiratory or skin sensitisation	Not classified (Based on available data, the classification criteria are not met)
Germ cell mutagenicity	Not classified (Based on available data, the classification criteria are not met)
Carcinogenicity	Not classified (Based on available data, the classification criteria are not met)
Reproductive toxicity	Not classified (Based on available data, the classification criteria are not met)
STOT-single exposure	Not classified (Based on available data, the classification criteria are not met)
STOT-repeated exposure	Not classified (Based on available data, the classification criteria are not met)
Aspiration hazard	Not classified (Based on available data, the classification criteria are not met)
Viscosity, kinematic	No data available
Symptoms/effects	Not expected to present a significant hazard under anticipated conditions of normal use.
Symptoms/effects after inhalation	Respiratory complaints.

SECTION 12: Ecological information

12.1. Toxicity

Ecology - general	The product is not considered harmful to aquatic organisms nor to cause long-term adverse effects in the environment.
-------------------	-----------------------------------------------------------------------------------------------------------------------

Carbon dioxide (124-38-9)	
LC50 - Fish [1]	35 mg/l (96 h; Salmo gairdneri; Literature data)

12.2. Persistence and degradability

GC FX 3	
Persistence and degradability	Not established.
Carbon dioxide (124-38-9)	
Persistence and degradability	Not applicable.
argon (7440-37-1)	
Not rapidly degradable	
Persistence and degradability	Not applicable.

12.3. Bioaccumulative potential

Carbon dioxide (124-38-9)	
Partition coefficient n-octanol/water (Log Pow)	0.83 (Measured)

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

argon (7440-37-1)	
Partition coefficient n-octanol/water (Log Pow)	0.74 (Measured)

12.4. Mobility in soil

No additional information available

12.5. Other adverse effects

Effect on global warming	No known effects from this product.
Other information	Avoid release to the environment.

SECTION 13: Disposal considerations

13.1. Disposal methods

Waste treatment methods	Dispose of contents/container in accordance with licensed collector's sorting instructions.
Product/Packaging disposal recommendations	Dispose in a safe manner in accordance with local/national regulations.

SECTION 14: Transport information

In accordance with ADR / IMDG / IATA / ADN / RID

ADR	IMDG	IATA	ADN	RID
14.1. UN number or ID number				
UN 1956	UN 1956	UN 1956	UN 1956	UN 1956
14.2. UN proper shipping name				
COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture)	COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture)	Compressed gas, n.o.s. (Argon, Carbon dioxide mixture)	COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture)	COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture)
Transport document description				
UN 1956 COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture), 2.2, (E)	UN 1956 COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture), 2.2	UN 1956 Compressed gas, n.o.s. (Argon, Carbon dioxide mixture), 2.2	UN 1956 COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture), 2.2	UN 1956 COMPRESSED GAS, N.O.S. (Argon, Carbon dioxide mixture), 2.2
14.3. Transport hazard class(es)				
2.2	2.2	2.2	2.2	2.2
14.4. Packing group				
Not applicable	Not applicable	Not applicable	Not applicable	Not applicable
14.5. Environmental hazards				
Dangerous for the environment: No	Dangerous for the environment: No Marine pollutant: No	Dangerous for the environment: No	Dangerous for the environment: No	Dangerous for the environment: No

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

ADR	IMDG	IATA	ADN	RID
No supplementary information available				

14.6. Special precautions for user

Overland transport

Classification code (ADR)	1A
Special provisions (ADR)	274, 378, 392
Limited quantities (ADR)	120ml
Excepted quantities (ADR)	E1
Packing instructions (ADR)	P200
Mixed packing provisions (ADR)	MP9
Portable tank and bulk container instructions (ADR)	(M)
Tank code (ADR)	CxBN(M)
Tank special provisions (ADR)	TA4, TT9
Vehicle for tank carriage	AT
Transport category (ADR)	3
Special provisions for carriage - Loading, unloading and handling (ADR)	CV9, CV10, CV36
Hazard identification number (Kemler No.)	20
Orange plates	

Tunnel restriction code (ADR) E

Transport by sea

Special provisions (IMDG)	274, 378, 392
Limited quantities (IMDG)	120 ml
Excepted quantities (IMDG)	E1
Packing instructions (IMDG)	P200
EmS-No. (Fire)	F-C
EmS-No. (Spillage)	S-V
Stowage category (IMDG)	A
MFAG-No	126

Air transport

PCA Excepted quantities (IATA)	E1
PCA Limited quantities (IATA)	Forbidden
PCA limited quantity max net quantity (IATA)	Forbidden
PCA packing instructions (IATA)	200
PCA max net quantity (IATA)	75kg
CAO packing instructions (IATA)	200
CAO max net quantity (IATA)	150kg
Special provisions (IATA)	A202
ERG code (IATA)	2L

Inland waterway transport

Classification code (ADN)	1A
Special provisions (ADN)	274, 378, 392, 655, 662
Limited quantities (ADN)	120 ml
Excepted quantities (ADN)	E1
Equipment required (ADN)	PP

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Number of blue cones/lights (ADN)	0
Rail transport	
Classification code (RID)	1A
Special provisions (RID)	274, 378, 392, 655, 662
Limited quantities (RID)	120ml
Excepted quantities (RID)	E1
Packing instructions (RID)	P200
Mixed packing provisions (RID)	MP9
Portable tank and bulk container instructions (RID)	(M)
Tank codes for RID tanks (RID)	CxBN(M)
Special provisions for RID tanks (RID)	TA4, TT9
Transport category (RID)	3
Special provisions for carriage - Loading, unloading and handling (RID)	CW9, CW10, CW36
Colis express (express parcels) (RID)	CE3
Hazard identification number (RID)	20

14.7. Maritime transport in bulk according to IMO instruments

Not applicable

SECTION 15: Regulatory information

15.1. US Federal regulations

All components of this product are present and listed as Active on the United States Environmental Protection Agency Toxic Substances Control Act (TSCA) inventory

15.2. International regulations

No additional information available

15.3. US State regulations

California Proposition 65 - This product does not contain any substances known to the state of California to cause cancer, developmental and/or reproductive harm

Component	State or local regulations
Carbon dioxide(124-38-9)	U.S. - Massachusetts - Right To Know List; U.S. - New Jersey - Right to Know Hazardous Substance List; U.S. - New York City - Right to Know Hazardous Substances List
argon(7440-37-1)	U.S. - Massachusetts - Right To Know List; U.S. - New Jersey - Right to Know Hazardous Substance List; U.S. - New York City - Right to Know Hazardous Substances List

SECTION 16: Other information

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

Revision date

08/16/2023

Data sources

European Chemicals Agency, <http://echa.europa.eu/>. manufacturer.

Full text of H-statements

H280	Contains gas under pressure; may explode if heated.
------	-----------------------------------------------------

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations


Abbreviations and acronyms	
CAS-No.	Chemical Abstract Service number
ADN	European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
ADR	European Agreement concerning the International Carriage of Dangerous Goods by Road
ATE	Acute Toxicity Estimate
CLP	Classification Labelling Packaging Regulation; Regulation (EC) No 1272/2008
DNEL	Derived-No Effect Level
EC50	Median effective concentration
ED	Endocrine disrupting properties
EC-No.	European Community number
EN	European Standard
IATA	International Air Transport Association
IMDG	International Maritime Dangerous Goods
IOELV	Indicative Occupational Exposure Limit Value
LC50	Median lethal concentration
LD50	Median lethal dose
NOEC	No-Observed Effect Concentration
OECD	Organisation for Economic Co-operation and Development
N.O.S.	Not Otherwise Specified
OEL	Occupational Exposure Limit
PBT	Persistent Bioaccumulative Toxic
PNEC	Predicted No-Effect Concentration
REACH	Registration, Evaluation, Authorisation and Restriction of Chemicals Regulation (EC) No 1907/2006
RID	Regulations concerning the International Carriage of Dangerous Goods by Rail
SDS	Safety Data Sheet
STP	Sewage treatment plant
TLM	Median Tolerance Limit
TRGS	Technical Rules for Hazardous Substances
VOC	Volatile Organic Compounds
WGK	Water Hazard Class
vPvB	Very Persistent and Very Bioaccumulative
NOAEL	No-Observed Adverse Effect Level
NOAEC	No-Observed Adverse Effect Concentration
LOAEL	Lowest Observed Adverse Effect Level

GC FX 3

Safety Data Sheet

according to Federal Register / Vol. 77, No. 58 / Monday, March 26, 2012 / Rules and Regulations

NFPA health hazard	0 - Materials that, under emergency conditions, would offer no hazard beyond that of ordinary combustible materials.
NFPA fire hazard	0 - Materials that will not burn under typical fire conditions, including intrinsically noncombustible materials such as concrete, stone, and sand.
NFPA reactivity	0 - Material that in themselves are normally stable, even under fire conditions.
NFPA specific hazard	SA - Materials that are simple asphyxiants.



Indication of changes:

Section	Changed item	Change	Comments
1	Emergency number	Modified	

SDS US HILTI

This information is based on our current knowledge and is intended to describe the product for the purposes of health, safety and environmental requirements only. It should not therefore be construed as guaranteeing any specific property of the product.