

Fast and accurate squaring and aligning.

PM 4-M Multi Line Laser

Precision, accuracy and versatility – the Hilti PM 4-M Multi Line Laser takes your leveling, plumbing and aligning applications to the next level. Featuring a rubberized tool body and the industry’s best service, the PM 4-M is designed to outlast the toughest jobsite conditions.



*Some limitations apply. Contact Hilti for details.

PULSE III POWER

Applications

- Leveling outlets, cable trays and pipes
- Leveling suspended ceilings
- Leveling and aligning doors and windows
- Transferring points
- Installing partition walls

Outperform

- Rotates around the center point for easy and fast aligning
- Fine-tuning knob for precise alignment
- Two vertical lines and one horizontal line for maximum versatility when leveling or aligning and in plumbing applications
- Pulse Power produces highly visible beams
- Free calibration service with Hilti Tool Fleet Management for highest tool accuracy

Outlast

- Large rubberized tool body to protect laser aperture and tool edges for increased durability
- Pendulum locking mechanism for added protection

Technical Data	PM 4-M
Fan angle	1 H at 180°; 1 V at 140°; 1 V at 240°
Accuracy at 30' / 10 m	1/16" / 2 mm
Self-leveling range	±3°
Self-leveling time	<3 sec
Laser class	635 nm, class 2 (IEC 825-1), class II (FDA 21 CFR)
IP protection class (except battery compartment)	IP 54 as per IEC 529 std
Operating temperature range	14°F to 122°F (-10°C to 50° C)
Operating time with alkaline battery	8.0 h
Dimensions (L x W x H)	4.9 x 4.9 x 7.4 in (124 x 124 x 187 mm)
Automatic switch off	After 60 min

Order Information

Description	Package Contents	Item No.
PM 4-M Multi Line Laser	Includes tool, tripod adapter, (4) AA batteries in Hilti case	02047072

Accessories

PMA 78 Universal Adapter	00411286
PMA 20 Compact Tripod	00411287
PMA 31 Laser Receiver	00411288
PMA 55 Target plate	00411290
PMA 74 Magnetic Bracket	00286150
PUA 60 Laser Visibility Glasses	00284988



Note: Red lines shown for illustration purposes only.

Hilti. Outperform. Outlast.