

## SPEED STRIPS CP 767

## SPEED PLUGS CP 777

### Product description

- CP 777: Pre-formed mineral wool plugs for 1.5", 2" and 3" decks
- CP 767: Pre-formed mineral wool strips suitable for joint applications

### Product features

- Pre-cut to industry standard size decking flutes
- Reduces material waste
- 3 sizes available
- Pre-cut — leaves no gaps or voids
- Smooth surface provides cost effective spray coverage
- Safer to use — no asbestos
- Up to 60% faster than castle cutting!
- CP 767: 4 PCF Density
- CP 777: 6 PCF Density

### Areas of application




- Top-of-wall

### Tested and approved

- UL Classified when used in conjunction with CP 606 Flexible Firestop Sealant, CFS-S SIL GG Gun Grade Silicone Sealant, or CFS-SP WB Firestop Joint Spray

### Installation instructions

- See Hilti literature or third-party listings for complete application and installation details



Description	Flute Dimensions (L x (Flute) x H)	Qty	Item No.
CP 777 1.5" Speed Plug	36" x (3.5" x 4.5") x 1.5"	18	371925
CP 777 2" Speed Plug	36" x (4.5" x 5.5") x 2"	18	340996
CP 777 3" Speed Plug	36" x (5" x 7") x 3"	18	340999
CP 767 2" Speed Strips (1 hour)	36" x 0.625" x 2"	84	374507
CP 767 2" Speed Strips (2 hour)	36" x 1.25" x 2"	42	374508
CP 767 4" Speed Strips (1 hour)	36" x 0.625" x 4"	42	374505
CP 767 4" Speed Strips (2 hour)	36" x 1.25" x 4"	21	374506