



All loading and design criteria supplied by customer is assumed accurate. Only the stated Design Assumptions were considered, and must be verified by the responsible Engineer of Record (EOR). The basis of Hilti component and connection design is the published data in the current Hilti Technical Guide, including material and cross-section properties, allowable load values, factors of safety, methods of calculation, and limiting factors. The EOR must verify suitability for any specific application, and the capacity of the supportive structure to receive the shown configuration and associated reaction loads. Modification to components and/or design may alter performance and must be evaluated by the EOR.

TYPICAL DETAIL TYPE:

CABLE TRAY SUPPORT

TYPICAL DETAIL DESCRIPTION:

CANTILEVER - SINGLE

DESIGNED BY:

KL

REVIEWED BY:

AJV

DRAWN BY:

GAB

ISSUE DATE:

02 JAN 15

REVISIONS:

NO.	DESCRIPTION:	DATE:
A	ORIGINAL ISSUE	02 JAN 15

TYPICAL DETAIL NOMENCLATURE:


CT-C06-S

DRAWING NUMBER:

01

SHEET:

1/1



01 ISOMETRIC
N.T.S.

02 ELEVATION
N.T.S.

03 SECTION
N.T.S.

- NOTE(S):**
- PRELIMINARY NOT FOR CONSTRUCTION
 - DESIGN ASSUMPTIONS:
 - DESIGN LOADS (STATIC, U.N.O.):
 - DL TRAY: 10 lbs/ft
 - DL CABLE: 100 lbs/ft
 - WL: 85 mph, Exp C, $I_p=1.15$
 - EL: SDS = 1.146, $I_p=1.25$
 - BUILDING CODE: LOS ANGELES COUNTY BUILDING CODE 2014
 - CORROSION RESISTANCE REQD.: HDG
 - MAX. SUPPORT SPACING = 4'-0"
 - ALL LOADS ASSUMED TO ACT AT CENTER LINE OF TRAY.
 - REFER TO COMPONENT MANUFACTURER'S IFUs FOR REQUIRED INSTALLATION INFO.
 - E.O.R. MUST BE NOTIFIED OF ANY DEVIATIONS FROM EXISTING/NEW SUBSTRATE CONDITIONS SHOWN HEREIN TO VALIDATE ACCEPTANCE OF THIS HILTI DESIGN PRIOR TO INSTALLATION.
 - INSTALL SUPPORT STRUCTURE TIGHT TO FACE OF CONCRETE.

No.	Unit Qty	Unit	Description	Box Qty	# Boxes Needed	Item No.
1	AS REQ'D	EA	GIRDER MI-90 3M	1	AS REQ'D	304798
2	AS REQ'D	EA	STRUT HS-158-12/HDG 10'	1	AS REQ'D	407570
3	4	EA	CHANNEL END CAP MEK RED	50	1	244886
4	4	EA	GIRDER END CAP MIA-EC90	25	1	432077
5	4	PR	CONNECTOR MIC-T	2	2	304807
6	2	EA	ONEHAND SCREW MIA-OH90	10	1	304889
7	2	EA	MI HEX NUT M12-F-SL-WS 3/4"	100	1	382897

\\hilti.com\US\TEAMS\installations\Projects\TYPICALS\TYPICAL LIBRARY\CABLE TRAY (CT)\CAD\CT-C06-S.dwg, 1/2/2015 2:39:35 PM